

# PE38WHT1000 Cut Sheet



HydroMode potable water tubing, polyethylene, white, 3/8in outside diameter, 1/4in inside diameter, NSF/ANSI 61, 1000ft reel.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PE38WHT1000>

---

## Technical Specifications

|                                     |                   |
|-------------------------------------|-------------------|
| <b>Brand</b>                        | HydroMode         |
| <b>Item</b>                         | Tubing            |
| <b>Working Fluid</b>                | Potable water     |
| <b>Material</b>                     | Polyethylene      |
| <b>Color</b>                        | White             |
| <b>Outside Diameter</b>             | 3/8in             |
| <b>Inside Diameter</b>              | 1/4in             |
| <b>Potable Water Certifications</b> | NSF/ANSI 61       |
| <b>UV stabilized</b>                | No                |
| <b>Working Length</b>               | 1000ft reel       |
| <b>Operating Pressure</b>           | 75 psi            |
| <b>Operating Temperature</b>        | -50 to +140 deg F |

---

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |