

PE38WHT100 Cut Sheet



HydroMode potable water tubing, polyethylene, white, 3/8in outside diameter, 1/4in inside diameter, NSF/ANSI 61, 100ft package.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PE38WHT100>

Technical Specifications

Brand	HydroMode
Item	Potable water Tubing
Material	Polyethylene
Color	White
Outside Diameter	3/8in
Inside Diameter	1/4in
Agency Approval	NSF/ANSI 61
UV stabilized	No
Working Length	100ft package
Operating Pressure	75 psi
Operating Temperature	-50 to +140 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document