

PE38WHT500 Cut Sheet



HydroMode potable water tubing, polyethylene, white, 3/8in outside diameter, 1/4in inside diameter, 500ft reel.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PE38WHT500>

Technical Specifications

Brand	HydroMode
Item	Tubing
Working Fluid	Potable water
Material	Polyethylene
Color	White
Outside Diameter	3/8in
Inside Diameter	1/4in
UV stabilized	No
Working Length	500ft reel
Operating Pressure	75 psi
Operating Temperature	-50 to +140 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document