

PE38YEL500 Cut Sheet



HydroMode potable water tubing, polyethylene, yellow, 3/8in outside diameter, 1/4in inside diameter, NSF/ANSI 61, 500ft reel.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PE38YEL500>

Technical Specifications

| | |
|------------------------------|----------------------|
| Brand | HydroMode |
| Item | Potable water Tubing |
| Material | Polyethylene |
| Color | Yellow |
| Outside Diameter | 3/8in |
| Inside Diameter | 1/4in |
| Agency Approval | NSF/ANSI 61 |
| UV stabilized | No |
| Working Length | 500ft reel |
| Operating Pressure | 75 psi |
| Operating Temperature | -50 to +140 deg F |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |