

PE516WHT1000 Cut Sheet



HydroMode potable water tubing, polyethylene, white, 5/16in (8mm) outside diameter, 0.236in inside diameter, NSF/ANSI 61, 1000ft reel.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PE516WHT1000>

Technical Specifications

| | |
|------------------------------|----------------------|
| Brand | HydroMode |
| Item | Potable water Tubing |
| Material | Polyethylene |
| Color | White |
| Outside Diameter | 5/16in (8mm) |
| Inside Diameter | 0.236in |
| Agency Approval | NSF/ANSI 61 |
| UV stabilized | No |
| Working Length | 1000ft reel |
| Operating Pressure | 75 psi |
| Operating Temperature | -50 to +140 deg F |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |