

PE532NAT100 Cut Sheet



HydroMode potable water tubing, polyethylene, natural, 5/32in (4mm) outside diameter, 0.106in inside diameter, NSF/ANSI 61, 100ft package.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PE532NAT100>

Technical Specifications

| | |
|-------------------------------------|-------------------|
| Brand | HydroMode |
| Item | Tubing |
| Working Fluid | Potable water |
| Material | Polyethylene |
| Color | Natural |
| Outside Diameter | 5/32in (4mm) |
| Inside Diameter | 0.106in |
| Potable Water Certifications | NSF/ANSI 61 |
| UV stabilized | No |
| Working Length | 100ft package |
| Operating Pressure | 75 psi |
| Operating Temperature | -50 to +140 deg F |

Agency Approvals

| | |
|-----------------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |