PESW-B18D15AX-R66 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

WEG Electric PESW series non-combination motor starter, 18A, 3-pole, 120 VAC (50/60Hz) coil voltage, bi-metallic, 11.0-17.0A adjustable, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/PESW-B18D15AX-R66

Technical Specifications

Brand	WEG Electric
Series	PESW
Item	Motor starter
Starter Type	Non-combination
Coil Voltage	120 VAC (50/60Hz)
Amperage Rating	18A
Voltage Rating	600 VAC
Horsepower Rating	10hp
Overload Type	Bi-metallic
Full Load Amperage Range	11.0-17.0A adjustable
Number of Poles	3

Power Poles	(3) N.O.
Auxiliary Contacts	(1) N.O./(1) N.C.
Trip Class	Trip Class 10
Phase Loss Sensitive	Yes
Ground Fault Protection	No
SCCR Rating	5kA SCCR
UL Rating	UL 508 rated
Enclosure Type	NEMA 4/4X
Mounting	Wall
Connection	Screw terminal
Includes	Start and stop/reset pushbuttons

Agency Approvals

UL Listed File #	E202315
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/PESW-B18D15AX-R66.pdf
See store item page for other formats.