

PESW-B32D39AX-R68 Cut Sheet



WEG Electric PESW series manual motor starter, pushbutton, 32A, 3-pole, 480 VAC (50/60Hz) coil voltage, thermal overload, 22.0-32.0A adjustable, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PESW-B32D39AX-R68>

Technical Specifications

| | |
|---------------------------------|----------------------------------|
| Brand | WEG Electric |
| Series | PESW |
| Item | Motor starter |
| Starter Type | Manual |
| Actuator Type | Pushbutton |
| Coil Voltage | 480 VAC (50/60Hz) |
| Amperage Rating | 32A |
| Voltage Rating | 600 VAC |
| Horsepower Rating | 20hp |
| Relay Type | Thermal overload |
| Operation Type | Bi-metallic |
| Full Load Amperage Range | 22.0-32.0A adjustable |
| Number of Poles | 3 |
| Power Poles | (3) N.O. |
| Auxiliary Contacts | (1) N.O./ (1) N.C. |
| Trip Class | Trip Class 10 |
| Phase Loss Sensitive | Yes |
| Ground Fault Protection | No |
| SCCR Rating | 5kA SCCR |
| UL Rating | UL 508 rated |
| Enclosure Type | NEMA 4/4X |
| Mounting | Wall |
| Connection | Screw terminal |
| Includes | Start and stop/reset pushbuttons |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E202315 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |