

PESW-B9D15AX-R62 Cut Sheet



WEG Electric PESW series manual motor starter, pushbutton, 9A, 3-pole, 120 VAC (50/60Hz) coil voltage, thermal overload, 5.6-8.0A Adjustable, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PESW-B9D15AX-R62>

Technical Specifications

Brand	WEG Electric	Number of Poles	3
Series	PESW	Power Poles	(3) N.O.
Item	Motor starter	Auxiliary Contacts	(1) N.O./ (1) N.C.
Starter Type	Manual	Trip Class	Trip Class 10
Actuator Type	Pushbutton	Phase Loss Sensitive	Yes
Coil Voltage	120 VAC (50/60Hz)	Ground Fault Protection	No
Amperage Rating	9A	SCCR Rating	5kA SCCR
Voltage Rating	600 VAC	UL Rating	UL 508 rated
Horsepower Rating	5hp	Enclosure Type	NEMA 4/4X
Relay Type	Thermal overload	Mounting	Wall
Operation Type	Bi-metallic	Connection	Screw terminal
Full Load Amperage Range	5.6-8.0A Adjustable	Includes	Start and stop/reset pushbuttons

Agency Approvals

UL Listed File #	E202315
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PESW-B9D15AX-R62.pdf>
See store item page for other formats.