

PESW-B9D39AX-R60 Cut Sheet



WEG Electric PESW series manual motor starter, pushbutton, 9A, 3-pole, 480 VAC (50/60Hz) coil voltage, thermal overload, 2.8-4.0A Adjustable, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PESW-B9D39AX-R60>

Technical Specifications

Brand	WEG Electric
Series	PESW
Item	Motor starter
Starter Type	Manual
Actuator Type	Pushbutton
Coil Voltage	480 VAC (50/60Hz)
Amperage Rating	9A
Voltage Rating	600 VAC
Horsepower Rating	2hp
Relay Type	Thermal overload
Operation Type	Bi-metallic
Full Load Amperage Range	2.8-4.0A Adjustable
Number of Poles	3
Power Poles	(3) N.O.
Auxiliary Contacts	(1) N.O./ (1) N.C.
Trip Class	Trip Class 10
Phase Loss Sensitive	Yes
Ground Fault Protection	No
SCCR Rating	5kA SCCR
UL Rating	UL 508 rated
Enclosure Type	NEMA 4/4X
Mounting	Wall
Connection	Screw terminal
Includes	Start and stop/reset pushbuttons

Agency Approvals

UL Listed File #	E202315
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document