

PESWS-B18V24AX-RM65 Cut Sheet



WEG Electric PESWS series manual motor starter, pushbutton, 18A, 2-pole, 208-240 VAC (60Hz)/180-208 VAC (50Hz) coil voltage, thermal overload, 10.0-15.0.A Adjustable, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PESWS-B18V24AX-RM65>

Technical Specifications

Brand	WEG Electric
Series	PESWS
Item	Motor starter
Starter Type	Manual
Actuator Type	Pushbutton
Coil Voltage	208-240 VAC (60Hz)/180-208 VAC (50Hz)
Amperage Rating	18A
Voltage Rating	600 VAC
Horsepower Rating	2hp
Relay Type	Thermal overload
Operation Type	Bi-metallic
Full Load Amperage Range	10.0-15.0.A Adjustable

Number of Poles	2
Power Poles	(2) N.O.
Auxiliary Contacts	(1) N.O./(1) N.C.
Trip Class	Trip Class 10
Phase Loss Sensitive	Yes
Ground Fault Protection	No
SCCR Rating	5kA SCCR
UL Rating	UL 508 rated
Enclosure Type	NEMA 4/4X
Mounting	Wall
Connection	Screw terminal
Includes	Start, stop and reset pushbuttons

Agency Approvals

UL Listed File #	E202315
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PESWS-B18V24AX-RM65.pdf>
See store item page for other formats.