

PESWS-B25D15AX-RM67 Cut Sheet



WEG Electric PESWS series manual motor starter, pushbutton, 25A, 2-pole, 120 VAC (50/60Hz) coil voltage, thermal overload, 15.0-23.0.A Adjustable, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PESWS-B25D15AX-RM67>

Technical Specifications

| | |
|---------------------------------|------------------------|
| Brand | WEG Electric |
| Series | PESWS |
| Item | Motor starter |
| Starter Type | Manual |
| Actuator Type | Pushbutton |
| Coil Voltage | 120 VAC (50/60Hz) |
| Amperage Rating | 25A |
| Voltage Rating | 600 VAC |
| Horsepower Rating | 3hp |
| Relay Type | Thermal overload |
| Operation Type | Bi-metallic |
| Full Load Amperage Range | 15.0-23.0.A Adjustable |

| | |
|--------------------------------|-----------------------------------|
| Number of Poles | 2 |
| Power Poles | (2) N.O. |
| Auxiliary Contacts | (1) N.O./ (1) N.C. |
| Trip Class | Trip Class 10 |
| Phase Loss Sensitive | Yes |
| Ground Fault Protection | No |
| SCCR Rating | 5kA SCCR |
| UL Rating | UL 508 rated |
| Enclosure Type | NEMA 4/4X |
| Mounting | Wall |
| Connection | Screw terminal |
| Includes | Start, stop and reset pushbuttons |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E202315 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PESWS-B25D15AX-RM67.pdf>
See store item page for other formats.