

PGB090-10A4 Cut Sheet



SureGear high-precision planetary gearbox, 10:1 ratio, right angle, 22mm diameter output shaft, nominal output torque 45 N-m (398 lb-in), 2-stage, 90mm frame. For use with SureServo and SureServo2 SV(2)L-210(B) motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PGB090-10A4>

Technical Specifications

| | |
|--------------------------------------|---|
| Brand | SureGear |
| Item | Gearbox |
| Application | High-precision |
| Gearbox Type | Planetary |
| Gear Ratio | 10:1 |
| Output Configuration | Right angle |
| Gearbox Output Shaft Diameter | 22mm |
| Nominal Output Torque | Nominal output torque 45 N-m (398 lb-in) |
| Number of Stages | 2 |
| Frame | 90mm |
| For Use With | SureServo and SureServo2 SV(2)L-210(B) motors |
| Includes | Input adapter bushing, motor mounting hardware and output shaft key |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |