

# PGCN23-10025 Cut Sheet



SureGear precision planetary gearbox, 100:1 ratio, inline, 0.375in diameter output shaft, nominal output torque 5 N-m (44 lb-in), 2-stage, NEMA 23 frame. For use with SureStep NEMA 23 motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PGCN23-10025>

## Technical Specifications

Brand	SureGear
Item	Gearbox
Application	Precision
Gearbox Type	Planetary
Gear Ratio	100:1
Output Configuration	Inline
Gearbox Output Shaft Diameter	0.375in
Nominal Output Torque	Nominal output torque 5 N-m (44 lb-in)
Number of Stages	2
Frame	NEMA 23
For Use With	SureStep NEMA 23 motors
Includes	Motor mounting hardware

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>