


# PGD047-10A1 Cut Sheet



SureGear high-precision planetary gearbox, 10:1 ratio, inline with hub style output, nominal output torque 6 N-m (53 lb-in), 1-stage, 47mm frame. For use with SureServo and SureServo2 SV(2)L-201(B) motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PGD047-10A1>

## Technical Specifications

<b>Brand</b>	SureGear
<b>Item</b>	Gearbox
<b>Application</b>	High-precision
<b>Gearbox Type</b>	Planetary
<b>Gear Ratio</b>	10:1
<b>Output Configuration</b>	Inline with hub style output
<b>Nominal Output Torque</b>	Nominal output torque 6 N-m (53 lb-in)
<b>Number of Stages</b>	1
<b>Frame</b>	47mm
<b>For Use With</b>	SureServo and SureServo2 SV(2)L-201(B) motors
<b>Includes</b>	Motor mounting hardware

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>