

PGD110-10A5 Cut Sheet



SureGear high-precision planetary gearbox, 10:1 ratio, inline with hub style output, nominal output torque 120 N-m (1062 lb-in), 1-stage, 110mm frame. For use with SureServo and SureServo2 SV(2)M-210(B) motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PGD110-10A5>

Technical Specifications

| | |
|-----------------------|---|
| Brand | SureGear |
| Item | Gearbox |
| Application | High-precision |
| Gearbox Type | Planetary |
| Gear Ratio | 10:1 |
| Output Configuration | Inline with hub style output |
| Nominal Output Torque | Nominal output torque 120 N-m (1062 lb-in) |
| Number of Stages | 1 |
| Frame | 110mm |
| For Use With | SureServo and SureServo2 SV(2)M-210(B) motors |
| Includes | Input adapter bushing and motor mounting hardware |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PGD110-10A5.pdf>
See store item page for other formats.