

# PGD110-25A4 Cut Sheet



SureGear high-precision planetary gearbox, 25:1 ratio, inline with hub style output, nominal output torque 180 N-m (1593 lb-in), 2-stage, 110mm frame. For use with SureServo and SureServo2 SV(2)L-210(B) motors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PGD110-25A4>

## Technical Specifications

|                              |   |
|------------------------------|---|
| <b>Brand</b>                 | SureGear  |
| <b>Item</b>                  | Gearbox   |
| <b>Application</b>           | High-precision                                    |
| <b>Gearbox Type</b>          | Planetary   |
| <b>Gear Ratio</b>            | 25:1  |
| <b>Output Configuration</b>  | Inline with hub style output                      |
| <b>Nominal Output Torque</b> | Nominal output torque 180 N-m (1593 lb-in)        |
| <b>Number of Stages</b>      | 2   |
| <b>Frame</b>                 | 110mm   |
| <b>For Use With</b>          | SureServo and SureServo2 SV(2)L-210(B) motors     |
| <b>Includes</b>              | Input adapter bushing and motor mounting hardware |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |