

PGU14 Cut Sheet



NITRA pneumatic push-to-connect fitting, inline pressure gauge, technopolymer body, (1) 1/4in push-to-connect inlet(s), (1) 1/4in push-to-connect outlet(s), 0-170 psi range.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PGU14>

Technical Specifications

| | |
|--------------------------|---------------------------|
| Brand | NITRA |
| Item | Fitting |
| Working Fluid | Air or inert gas |
| Fitting Connection Type | Push-to-connect |
| Fitting Function | Inline pressure gauge |
| Body Material | Technopolymer |
| Fitting Measurement Type | SAE |
| Inlet Port | (1) 1/4in push-to-connect |
| Outlet Port | (1) 1/4in push-to-connect |
| Pressure Range | 0-170 psi |
| Operating Temperature | -4 to 140 deg F |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PGU14.pdf>
See store item page for other formats.