

# PH1000MGJ Cut Sheet



Hammond control transformer, encapsulated core, 1 kVA, 1-phase, 208/277/380 VAC primary, 120/240 VAC secondary, 50/60 Hz, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PH1000MGJ>

## Technical Specifications

|                             |                 |
|-----------------------------|-----------------|
| <b>Brand</b>                | Hammond         |
| <b>Series</b>               | Imperator       |
| <b>Item</b>                 | Transformer     |
| <b>Transformer Type</b>     | Control         |
| <b>Core Type</b>            | Encapsulated    |
| <b>Power Rating</b>         | 1 kVA           |
| <b>Number of Phases</b>     | 1               |
| <b>Primary Voltage</b>      | 208/277/380 VAC |
| <b>Secondary Voltage</b>    | 120/240 VAC     |
| <b>Frequency</b>            | 50/60 Hz        |
| <b>Electrostatic Shield</b> | No              |
| <b>Mounting</b>             | Panel           |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E50394                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LR 3902                                |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |