

PH250PG Cut Sheet



Hammond control transformer, encapsulated core, 250 VA, 1-phase, 120/240 VAC primary, 12/24 VAC secondary, 50/60 Hz, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PH250PG>

Technical Specifications

| | |
|-----------------------------|--------------|
| Brand | Hammond |
| Series | Imperator |
| Item | Transformer |
| Transformer Type | Control |
| Core Type | Encapsulated |
| Power Rating | 250 VA |
| Number of Phases | 1 |
| Primary Voltage | 120/240 VAC |
| Secondary Voltage | 12/24 VAC |
| Frequency | 50/60 Hz |
| Electrostatic Shield | No |
| Mounting | Panel |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E50394 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |