

PH50MLI Cut Sheet



Hammond control transformer, encapsulated core, 50 VA, 1-phase, 240/480 VAC primary, 25/120 VAC secondary, 50/60 Hz, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PH50MLI>

Technical Specifications

Brand	Hammond
Series	Imperator
Item	Transformer
Transformer Type	Control
Core Type	Encapsulated
Power Rating	50 VA
Number of Phases	1
Primary Voltage	240/480 VAC
Secondary Voltage	25/120 VAC
Frequency	50/60 Hz
Fused	No
Electrostatic Shield	No
Mounting	Panel
Connection	Screw terminal

Agency Approvals

UL Listed File #	E50394
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	003902
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document