

# PH50MQMJ Cut Sheet



Hammond control transformer, encapsulated core, 50 VA, 1-phase, 240/480 VAC primary, 120/240 VAC secondary, 50/60 Hz, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PH50MQMJ>

## Technical Specifications

|                             |              |
|-----------------------------|--------------|
| <b>Brand</b>                | Hammond      |
| <b>Series</b>               | Imperator    |
| <b>Item</b>                 | Transformer  |
| <b>Transformer Type</b>     | Control      |
| <b>Core Type</b>            | Encapsulated |
| <b>Power Rating</b>         | 50 VA        |
| <b>Number of Phases</b>     | 1            |
| <b>Primary Voltage</b>      | 240/480 VAC  |
| <b>Secondary Voltage</b>    | 120/240 VAC  |
| <b>Frequency</b>            | 50/60 Hz     |
| <b>Electrostatic Shield</b> | No           |
| <b>Mounting</b>             | Panel        |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E50394                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |