

PH75MQMJ Cut Sheet



Hammond control transformer, encapsulated core, 75 VA, 1-phase, 240/480 VAC primary, 120/240 VAC secondary, 50/60 Hz, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PH75MQMJ>

Technical Specifications

Brand	Hammond
Series	Imperator
Item	Transformer
Transformer Type	Control
Core Type	Encapsulated
Power Rating	75 VA
Number of Phases	1
Primary Voltage	240/480 VAC
Secondary Voltage	120/240 VAC
Frequency	50/60 Hz
Fused	No
Electrostatic Shield	No
Mounting	Panel
Connection	Screw terminal

Agency Approvals

UL Listed File #	E50394
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PH75MQMJ.pdf>
See store item page for other formats.