

# PK-103-121-CASS Cut Sheet



Sifam Tinsley MCS switchboard meter, 4.5 in analog dial display, 0-1000 A DC, voltage input, shunt rated, pivot and jewel, round 4-hole mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PK-103-121-CASS>

## Technical Specifications

|                                   |                                |
|-----------------------------------|--------------------------------|
| <b>Brand</b>                      | Sifam Tinsley                  |
| <b>Item</b>                       | Switchboard meter              |
| <b>Series</b>                     | MCS                            |
| <b>Display Type</b>               | 4.5 in analog dial             |
| <b>Scale</b>                      | 0-1000 A DC                    |
| <b>Case Type</b>                  | Black powder coated steel case |
| <b>Input Voltage Signal Range</b> | 0-50 mVDC (shunt)              |
| <b>Input Type</b>                 | Shunt rated                    |

|                             |                                   |
|-----------------------------|-----------------------------------|
| <b>Movement Type</b>        | Pivot and jewel                   |
| <b>Accuracy</b>             | ±1% of full scale                 |
| <b>Mounting</b>             | Round 4-hole                      |
| <b>Mounting Hole Size</b>   | 4.06 in                           |
| <b>IP Rating</b>            | IP54                              |
| <b>NEMA Rating</b>          | 3                                 |
| <b>Connection</b>           | #10-32 UNF terminal stud with nut |
| <b>Applicable Standards</b> | ANSI C39.1                        |

## Agency Approvals

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>UL Listed File #</b>     | E471457                                |
| <b>UL Recognized File #</b> | N/A                                    |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | N/A                                    |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/PK-103-121-CASS.pdf>  
See store item page for other formats.