

PK-103-131-LSPK-C7 Cut Sheet



Sifam Tinsley MCS switchboard meter, 4.5 in analog dial display, 0-100 A AC, current input, transformer rated, pivot and jewel, round 4-hole mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PK-103-131-LSPK-C7>

Technical Specifications

Brand	Sifam Tinsley
Item	Switchboard meter
Series	MCS
Display Type	4.5 in analog dial
Scale	0-100 A AC
Case Type	Black powder coated steel case
Input Current Signal Range	0-5 A AC
Input Type	Transformer rated

Movement Type	Pivot and jewel
Accuracy	±1% of full scale
Mounting	Round 4-hole
Mounting Hole Size	4.06 in
IP Rating	IP54
NEMA Rating	3
Connection	#10-32 UNF terminal stud with nut
Applicable Standards	ANSI C39.1

Agency Approvals

UL Listed File #	E471457
UL Recognized File #	N/A
UL Hazardous File #	None
CE	View CE declarations
CSA File #	N/A
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PK-103-131-LSPK-C7.pdf>
See store item page for other formats.