

# PK-103-402-FEAD-C6 Cut Sheet



Sifam Tinsley MCS switchboard meter, 4.5 in analog dial display, 0.5-1-0.5 power factor, 3-phase voltage and current input, transformer rated, pivot and jewel, round 4-hole mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PK-103-402-FEAD-C6>

## Technical Specifications

<b>Brand</b>	Sifam Tinsley
<b>Item</b>	Switchboard meter
<b>Series</b>	MCS
<b>Display Type</b>	4.5 in analog dial
<b>Scale</b>	0.5-1-0.5 power factor
<b>Case Type</b>	Black powder coated steel case
<b>Input Current Signal Range</b>	0-5 A AC
<b>Input Voltage Signal Range</b>	0-240 VAC
<b>Input Type</b>	Transformer rated

<b>Movement Type</b>	Pivot and jewel
<b>Accuracy</b>	±1%
<b>Mounting</b>	Round 4-hole
<b>Mounting Hole Size</b>	4.06 in
<b>IP Rating</b>	IP54
<b>NEMA Rating</b>	3
<b>Connection</b>	#10-32 UNF terminal stud with nut
<b>Applicable Standards</b>	ANSI C39.1
<b>Additional Information</b>	3ph 3 or 4 wire 60Hz balanced systems only

## Agency Approvals

<b>UL Listed File #</b>	E471457
<b>UL Recognized File #</b>	N/A
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	N/A
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/PK-103-402-FEAD-C6.pdf>  
See store item page for other formats.