

PK-250-324-ECSC Cut Sheet



Sifam Tinsley Smartlook panel meter, 3.5 in analog dial display, 0-400 A DC, voltage input, shunt rated, moving coil, round 3-hole mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PK-250-324-ECSC>

Technical Specifications

Brand	Sifam Tinsley
Item	Panel meter
Series	Smartlook
Display Type	3.5 in analog dial
Scale	0-400 A DC
Case Type	Polycarbonate
Input Voltage Signal Range	0-50 mVDC (shunt)
Input Type	Shunt rated

Movement Type	Moving coil
Accuracy	±1.5% of full scale
Mounting	Round 3-hole
Mounting Hole Size	2.71 in
IP Rating	IP55
NEMA Rating	4
Connection	#10-32 UNF terminal stud with nut
Applicable Standards	ANSI C39.1 and EN/IEC 60051-1

Agency Approvals

UL Listed File #	None
UL Recognized File #	E471457
UL Hazardous File #	None
CE	View CE declarations
CSA File #	263805
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PK-250-324-ECSC.pdf>
See store item page for other formats.