

PK-250-344-PZUL Cut Sheet



Sifam Tinsley Smartlook panel meter, 3.5 in analog dial display, 0–5250 VAC, voltage input, transformer rated, moving iron, round 3-hole mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PK-250-344-PZUL>

Technical Specifications

Brand	Sifam Tinsley
Item	Panel meter
Series	Smartlook
Display Type	3.5 in analog dial
Scale	0–5250 VAC
Case Type	Polycarbonate
Input Voltage Signal Range	0–150 VAC
Input Type	Transformer rated

Movement Type	Moving iron
Accuracy	±1.5% of full scale
Mounting	Round 3-hole
Mounting Hole Size	2.71 in
IP Rating	IP55
NEMA Rating	4
Connection	#10-32 UNF terminal stud with nut
Applicable Standards	ANSI C39.1 and EN/IEC 60051–1

Agency Approvals

UL Listed File #	None
UL Recognized File #	E471457
UL Hazardous File #	None
CE	View CE declarations
CSA File #	263805
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PK-250-344-PZUL.pdf>
See store item page for other formats.