

PK-260-200-HFHF Cut Sheet



Sifam Tinsley Contender panel meter, 2.5 in analog dial display, 0–20 mA, current input, self contained, moving coil, round 4-hole mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PK-260-200-HFHF>

Technical Specifications

Brand	Sifam Tinsley
Item	Panel meter
Series	Contender
Display Type	2.5 in analog dial
Scale	0–20 mA
Case Type	Polycarbonate
Input Current Signal Range	0–20 mA DC
Input Type	Self contained

Movement Type	Moving coil
Accuracy	±1.5% of full scale
Mounting	Round 4-hole
Mounting Hole Size	2.16 in
IP Rating	IP54
NEMA Rating	3
Connection	#10-32 UNF terminal stud with nut
Applicable Standards	ANSI C39.1 and EN/IEC 60051–1

Agency Approvals

UL Listed File #	None
UL Recognized File #	E471457
UL Hazardous File #	None
CE	View CE declarations
CSA File #	263805
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PK-260-200-HFHF.pdf>
See store item page for other formats.