

PK-260-224-ECRL Cut Sheet



Sifam Tinsley Contender panel meter, 2.5 in analog dial display, 0–200 A DC, voltage input, shunt rated, moving coil, round 4-hole mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PK-260-224-ECRL>

Technical Specifications

Brand	Sifam Tinsley	Movement Type	Moving coil
Item	Panel meter	Accuracy	±1.5% of full scale
Series	Contender	Mounting	Round 4-hole
Display Type	2.5 in analog dial	Mounting Hole Size	2.16 in
Scale	0–200 A DC	IP Rating	IP54
Case Type	Polycarbonate	NEMA Rating	3
Input Voltage Signal Range	0–50 mVDC (shunt)	Connection	#10-32 UNF terminal stud with nut
Input Type	Shunt rated	Applicable Standards	ANSI C39.1 and EN/IEC 60051–1

Agency Approvals

UL Listed File #	None
UL Recognized File #	E471457
UL Hazardous File #	None
CE	View CE declarations
CSA File #	263805
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PK-260-224-ECRL.pdf>
See store item page for other formats.