

PK-260-320-NDND Cut Sheet



Sifam Tinsley Contender panel meter, 3.5 in analog dial display, 0-15 VDC, voltage input, self contained, moving coil, round 4-hole mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PK-260-320-NDND>

Technical Specifications

Brand	Sifam Tinsley
Item	Panel meter
Series	Contender
Display Type	3.5 in analog dial
Scale	0-15 VDC
Case Type	Polycarbonate
Input Voltage Signal Range	0-15 VDC
Input Type	Self contained

Movement Type	Moving coil
Accuracy	±1.5% of full scale
Mounting	Round 4-hole
Mounting Hole Size	2.16 in
IP Rating	IP54
NEMA Rating	3
Connection	#10-32 UNF terminal stud with nut
Applicable Standards	ANSI C39.1 and EN/IEC 60051-1

Agency Approvals

UL Listed File #	None
UL Recognized File #	E471457
UL Hazardous File #	None
CE	View CE declarations
CSA File #	263805
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PK-260-320-NDND.pdf>
See store item page for other formats.