

PK-264-350-AJAJ Cut Sheet



Sifam Tinsley Contender panel meter, 3.5 in analog dial display, 45–65 Hz, frequency input, self contained, pivot and jewel, round 4-hole mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PK-264-350-AJAJ>

Technical Specifications

Brand	Sifam Tinsley
Item	Panel meter
Series	Contender
Display Type	3.5 in analog dial
Scale	45–65 Hz
Case Type	Polycarbonate
Input Voltage Signal Range	0–120 VAC
Input Type	Self contained

Movement Type	Pivot and jewel
Accuracy	±0.5% of end scale value
Mounting	Round 4-hole
Mounting Hole Size	2.16 in
IP Rating	IP54
NEMA Rating	3
Connection	#10-32 UNF terminal stud with nut
Applicable Standards	ANSI C39.1 and EN/IEC 60051–1

Agency Approvals

UL Listed File #	None
UL Recognized File #	E471457
UL Hazardous File #	None
CE	View CE declarations
CSA File #	263805
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PK-264-350-AJAJ.pdf>
See store item page for other formats.