

PLS-4P-1-230 Cut Sheet



ProSense rotating paddle bulk solids level switch, 100mm insertion length, 1-1/4in male NPT process connection, (1) SPDT relay, 230 VAC operating voltage. Hinged paddle included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PLS-4P-1-230>

Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Rotating paddle
Media Type	Bulk solids
Mounting	Any orientation
Insertion Length	100mm
Process Connection	1-1/4in male NPT
Process Temperature	-4 to 176F (-20 to 80C)
Output	(1) SPDT relay
Operating Voltage	230 VAC
Wetted Parts	PBT, nitrile rubber, stainless steel
Electrical Connection	Spring connection terminals
Includes	Hinged paddle

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document