

# PLS-4P-2-115-HAZ Cut Sheet



ProSense rotating paddle bulk solids level switch, 200mm insertion length, 1-1/4in male NPT process connection, (1) SPDT relay, 115 VAC operating voltage. Hinged paddle included. Hazardous location rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PLS-4P-2-115-HAZ>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Level switch
<b>Sensor Type</b>	Rotating paddle
<b>Media Type</b>	Bulk solids
<b>Mounting</b>	Any orientation
<b>Insertion Length</b>	200mm
<b>Process Connection</b>	1-1/4in male NPT
<b>Process Temperature</b>	-4 to 176F (-20 to 80C)
<b>Output</b>	(1) SPDT relay
<b>Operating Voltage</b>	115 VAC
<b>Wetted Parts</b>	PBT, nitrile rubber, stainless steel
<b>Electrical Connection</b>	Spring connection terminals
<b>Includes</b>	Hinged paddle
<b>Application</b>	Hazardous location rated

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">FM Approval Document</a>