

PLS-4P-R-115 Cut Sheet



ProSense rotating paddle bulk solids level switch, 2000mm rope insertion length, 1-1/4in male NPT process connection, (1) SPDT relay, 115 VAC operating voltage. Hinged paddle included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PLS-4P-R-115>

Technical Specifications

Brand	ProSense	Output	(1) SPDT relay
Item	Level switch	Operating Voltage	115 VAC
Sensor Type	Rotating paddle	Housing Size	103mm diameter
Media Type	Bulk solids	Housing Material	Polycarbonate
Mounting	Any orientation	IP Rating	IP66
Insertion Length	2000mm rope	Wetted Parts	PBT, nitrile rubber, stainless steel
Process Connection	1-1/4in male NPT	Electrical Connection	Spring connection terminals
Process Temperature	-4 to 176 deg F	Includes	Hinged paddle

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PLS-4P-R-115.pdf>
See store item page for other formats.