

# PLS-4P-R-230 Cut Sheet



ProSense rotating paddle bulk solids level switch, 2000mm rope insertion length, 1-1/4in male NPT process connection, (1) SPDT relay, 230 VAC operating voltage. Hinged paddle included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PLS-4P-R-230>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Level switch
<b>Sensor Type</b>	Rotating paddle
<b>Media Type</b>	Bulk solids
<b>Mounting</b>	Any orientation
<b>Insertion Length</b>	2000mm rope
<b>Process Connection</b>	1-1/4in male NPT
<b>Process Temperature</b>	-4 to 176F (-20 to 80C)
<b>Output</b>	(1) SPDT relay
<b>Operating Voltage</b>	230 VAC
<b>Wetted Parts</b>	PBT, nitrile rubber, stainless steel
<b>Electrical Connection</b>	Spring connection terminals
<b>Includes</b>	Hinged paddle

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>