

PLTC3-20-1S-1 Cut Sheet



Quabbin instrumentation cable, overall shielded, PLTC, 300V, 1 twisted pair, 20 AWG, PVC conductor insulation material, black and white numbered pairs, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PLTC3-20-1S-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Instrumentation
UL Wire/Cable Type	PLTC
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	1 twisted pair
Conductor Size	20 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC

Conductor Insulation Color	Black and white numbered pairs
Shielding	Overall shielded
Jacket Material	PVC
Jacket Color	Black
Nominal Overall Cable Diameter	0.203in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 25 to 99ft = Coil• 100 to 945ft = 14 x 7in Reel• 946 to 1350ft = 14 x 10in Reel• 1351 to 2075ft = 16 x 10in Reel• 2076 to 2895ft = 18 x 10in Reel• 2896 to 3765ft = 18 x 13in Reel• 3766 to 5000ft = 24 x 17in Wooden Reel

Agency Approvals

UL Listed File #	E247880,E70148,E118830
UL Recognized File #	E69976
UL Hazardous File #	none
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement