

# PLTC3-20-4S-1 Cut Sheet



Quabbin instrumentation cable, overall shielded, PLTC, 300V, 4 twisted pairs, 20 AWG, PVC conductor insulation material, black and white numbered pairs, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PLTC3-20-4S-1>

## Technical Specifications

<b>Brand</b>	Quabbin
<b>Item</b>	Cable
<b>Wire/Cable Type</b>	Instrumentation
<b>UL Wire/Cable Type</b>	PLTC
<b>Application</b>	General purpose
<b>Flexibility</b>	Semi-flexible
<b>Voltage Rating</b>	300V
<b>Conductors</b>	4 twisted pairs
<b>Conductor Size</b>	20 AWG
<b>Conductor Stranding</b>	7-stranded
<b>Conductor Material</b>	Tinned copper
<b>Conductor Insulation Material</b>	PVC
<b>Conductor Insulation Color</b>	Black and white numbered pairs

<b>Shielding</b>	Overall shielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Black
<b>Nominal Overall Cable Diameter</b>	0.333in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	<ul style="list-style-type: none"><li>• 25 to 75ft = Coil</li><li>• 76 to 350ft = 14 x 7in Reel</li><li>• 351 to 500ft = 14 x 10in Reel</li><li>• 501 to 770ft = 16 x 10in Reel</li><li>• 771 to 1075ft = 18 x 10in Reel</li><li>• 1076 to 1400ft = 18 x 13in Reel</li><li>• 1401 to 3130ft = 24 x 17in Wooden Reel</li><li>• 3131 to 5000ft = 30 x 17in Wooden Reel</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	E247880,E70148,E118830
<b>UL Recognized File #</b>	E69976
<b>UL Hazardous File #</b>	none
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>