

PLTC3-20-8S-1 Cut Sheet



Quabbin instrumentation cable, overall shielded, PLTC, 300V, 8 twisted pairs, 20 AWG, PVC conductor insulation material, black and white numbered pairs, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PLTC3-20-8S-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Instrumentation
UL Wire/Cable Type	PLTC
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	8 twisted pairs
Conductor Size	20 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black and white numbered pairs

Shielding	Overall shielded
Jacket Material	PVC
Jacket Color	Black
Nominal Overall Cable Diameter	0.453in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 190ft = 14 x 7in Reel, 191 to 270ft = 14 x 10in Reel, 271 to 420ft = 16 x 10in Reel, 421 to 590ft = 18 x 10in Reel, 591 to 770ft = 18 x 13in Reel, 771 to 1660ft = 24 x 17in Wooden Reel, 1661 to 2730ft = 30 x 17in Wooden Reel, 2731 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E247880,E70148,E118830
UL Recognized File #	E69976
UL Hazardous File #	none
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement