


PM-0124-010-0 Cut Sheet



BLOCK Power Mini series switching power supply, 24 VDC @ 1A/24W (adjustable), 100-240 VAC nominal input, 1-phase, enclosed, plastic housing, 35mm DIN rail mount, push terminals, NEC Class 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PM-0124-010-0>

Technical Specifications

Brand	BLOCK
Item	Power supply
Series	Power Mini
Power Supply Type	Switching
Efficiency	86% @115 VAC
Output Configuration	Single output
Output	24 VDC @ 1A/24W (adjustable)
Output Voltage Range	23-28.5 VDC
Input voltage range	85-264 VAC
Number of Input Phases	1
Protection Type(s)	<ul style="list-style-type: none">• overvoltage• short circuit

Remote On/Off	No
Voltage Monitoring	Yes
Enclosure Type	Enclosed
Housing Material	Plastic
IP Rating	IP20
Mounting	35mm DIN rail
Connector Type	Push terminals
NEC Class 2	Yes
Integrated UPS Battery Control	No
Operating Temperature	-25 to 70 deg C

Agency Approvals

UL Listed File #	E219022
UL Recognized File #	E213214
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PM-0124-010-0.pdf>
See store item page for other formats.