

# PM-0624-100-0 Cut Sheet



BLOCK redundancy module, 2 inputs, 24 VDC nominal input, 10-36 VDC output, 10A, alarm contact for operation monitoring, push terminals. Requires BLOCK Power Mini Power Supplies.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PM-0624-100-0>

## Technical Specifications

<b>Brand</b>	BLOCK
<b>Item</b>	Redundancy module
<b>Number of Inputs</b>	2
<b>Nominal Input Voltage</b>	24 VDC
<b>Input voltage range</b>	10-36 VDC
<b>Nominal Output Voltage</b>	24 VDC
<b>Output Voltage Range</b>	10-36 VDC
<b>Amperage Rating</b>	10A

<b>Alarm Contact for Operation Monitoring</b>	Yes
<b>Active Current Sharing</b>	No
<b>Housing Material</b>	Plastic
<b>Mounting</b>	35mm DIN rail
<b>Connector Type</b>	Push terminals
<b>Requires</b>	BLOCK Power Mini Power Supplies

## Agency Approvals

<b>UL Listed File #</b>	E219022
<b>UL Recognized File #</b>	E213214
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/PM-0624-100-0.pdf>  
See store item page for other formats.