

# PMC21-CA1M1QFVXJA Cut Sheet



Endress+Hauser Cerabar pressure transmitter, 0 to 240 psig range, +/- 0.3% accuracy, ceramic sensing element, FKM seal(s), 4-20 mA analog output, 1/2in male NPT or 1/4in female NPT process connection, 10 to 30 VDC operating voltage, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PMC21-CA1M1QFVXJA>

## Technical Specifications

<b>Brand</b>	Endress+Hauser
<b>Item</b>	Pressure transmitter
<b>Series</b>	Cerabar
<b>Pressure Range</b>	0 to 240 psig
<b>Accuracy</b>	+/- 0.3% of full range
<b>Sensing Element Material</b>	Ceramic
<b>Seal Material</b>	FKM
<b>Analog Output</b>	4-20 mA
<b>Process Connection</b>	1/2in male NPT or 1/4in female NPT
<b>Operating Voltage</b>	10 to 30 VDC
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Media Type</b>	Liquid and gases
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	053988_C_000
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/PMC21-CA1M1QFVXJA.pdf>  
See store item page for other formats.