

PMP11-CA1L1RFVXJ Cut Sheet



Endress+Hauser Cerabar pressure transmitter, 0 to 375 psig range, +/- 0.5% accuracy, stainless steel sensing element, 4-20 mA analog output, 1/2in male NPT or 1/4in female NPT process connection, 10 to 30 VDC operating voltage, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PMP11-CA1L1RFVXJ>

Technical Specifications

| | |
|---------------------------------|------------------------------------|
| Brand | Endress+Hauser |
| Item | Pressure transmitter |
| Series | Cerabar |
| Pressure Range | 0 to 375 psig |
| Accuracy | +/- 0.5% of full range |
| Sensing Element Material | Stainless steel |
| Analog Output | 4-20 mA |
| Process Connection | 1/2in male NPT or 1/4in female NPT |
| Operating Voltage | 10 to 30 VDC |
| Electrical Connection | 4-pin M12 quick-disconnect |
| Media Type | Liquid and gases |
| Additional Information | Purchase cable separately |

Agency Approvals

| | |
|-----------------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 053988_C_000 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PMP11-CA1L1RFVXJ.pdf>
See store item page for other formats.