

PMP11-CA1V1NFVXJ Cut Sheet



Endress+Hauser Cerabar pressure transmitter, 0 to 90 psig range, +/- 0.5% accuracy, stainless steel sensing element, 4-20 mA analog output, 1/2in male NPT or 1/4in female NPT process connection, 10-30 VDC operating voltage, ISO4400 valve plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PMP11-CA1V1NFVXJ>

Technical Specifications

Brand	Endress+Hauser
Item	Pressure transmitter
Series	Cerabar
Pressure Range	0 to 90 psig
Accuracy	+/- 0.5% of full range
Sensing Element Material	Stainless steel
Analog Output	4-20 mA
Process Connection	1/2in male NPT or 1/4in female NPT
Operating Voltage	10-30 VDC
Electrical Connection	ISO4400 valve plug
Media Type	Liquid and gases

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	053988_C_000
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PMP11-CA1V1NFVXJ.pdf>
See store item page for other formats.