

# PMP23-CA1M1MF3CJ Cut Sheet



Endress+Hauser Cerabar pressure transmitter, 0 to 60 psig range, +/- 0.3% accuracy, stainless steel sensing element, Output: 4-20 mA, 1-1/2in sanitary tri-clamp process connection, 10 to 30 VDC operating voltage, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PMP23-CA1M1MF3CJ>

## Technical Specifications

|                                 |                            |
|---------------------------------|----------------------------|
| <b>Brand</b>                    | Endress+Hauser             |
| <b>Item</b>                     | Pressure transmitter       |
| <b>Series</b>                   | Cerabar                    |
| <b>Pressure Range</b>           | 0 to 60 psig               |
| <b>Accuracy</b>                 | +/- 0.3% of full range     |
| <b>Sensing Element Material</b> | Stainless steel            |
| <b>Output</b>                   | 4-20 mA                    |
| <b>Process Connection</b>       | 1-1/2in sanitary tri-clamp |
| <b>Operating Voltage</b>        | 10 to 30 VDC               |
| <b>Electrical Connection</b>    | 4-pin M12 quick-disconnect |
| <b>Media Type</b>               | Liquid and gases           |
| <b>Additional Information</b>   | Purchase cable separately  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 053988_C_000                           |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/PMP23-CA1M1MF3CJ.pdf>  
See store item page for other formats.