

PMRU-2C-600A Cut Sheet



ProSense phase monitor relay, 3-phase, 35mm DIN rail mount, 460-600 VAC input voltage, DPDT, 10A contact rating, screw terminal(s), LED indicator(s), phase reversal, phase loss, phase unbalance, overvoltage and undervoltage protection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PMRU-2C-600A>

Technical Specifications

| | |
|---------------------|---------------|
| Brand | ProSense |
| Item | Relay |
| Relay Type | Phase monitor |
| Number of Phases | 3 |
| Mounting | 35mm DIN rail |
| Relay Housing Type | Finger-safe |
| Input Voltage | 460-600 VAC |
| Relay Configuration | DPDT |

| | |
|--------------------|--|
| Connector Type | Screw terminal(s) |
| Contact Rating | 10A |
| Indicator | LED |
| Protection Type(s) | <ul style="list-style-type: none">• phase reversal• phase loss• phase unbalance• overvoltage• undervoltage |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E191059 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PMRU-2C-600A.pdf>
See store item page for other formats.