


PMTC-14U-4BK-1 Cut Sheet



Southwire flexible power/control cable, unshielded, 4 conductors (includes ground), 14 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PMTC-14U-4BK-1>

Technical Specifications

Brand	Southwire
Item	Cable
Wire/Cable Type	Power/control
UL Wire/Cable Type	TC, TC-ER, WTTC and MTW
Application	General purpose
Flexibility	Flexible
Voltage Rating	600V (Types TC, TC-ER, MTW), 1000V (Type WTTC)
Conductors	4 conductors (includes ground)
Conductor Size	14 AWG
Conductor Stranding	41-stranded
Conductor Material	Bare copper
Conductor Insulation Material	PVC/Nylon
Conductor Insulation Color	Black with white numbers and green/yellow ground

Shielding	Unshielded
Jacket Material	TPE
Jacket Color	Black
Nominal Overall Cable Diameter	0.37in
Bulk Length	Cut to length
Package Type	1 to 75ft = Coil, 76 to 280ft = 14 x 7in Reel, 281 to 400ft = 14 x 10in Reel, 401 to 630ft = 16 x 10in Reel, 631 to 890ft = 18 x 10in Reel, 891 to 1150ft = 18 x 13in Reel, 1151 to 2480ft = 24 x 17in Wooden Reel, 2481 to 4090ft = 30 x 17in Wooden Reel, 4091 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E75755
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement