


# PMTC-14U-9BK-1 Cut Sheet



Southwire flexible power/control cable, unshielded, 9 conductors (includes ground), 14 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PMTC-14U-9BK-1>

## Technical Specifications

<b>Brand</b>	Southwire
<b>Item</b>	Cable
<b>Wire/Cable Type</b>	Power/control
<b>UL Wire/Cable Type</b>	TC, TC-ER, WTTC and MTW
<b>Application</b>	General purpose
<b>Flexibility</b>	Flexible
<b>Voltage Rating</b>	600V (Types TC, TC-ER, MTW), 1000V (Type WTTC)
<b>Conductors</b>	9 conductors (includes ground)
<b>Conductor Size</b>	14 AWG
<b>Conductor Stranding</b>	41-stranded
<b>Conductor Material</b>	Bare copper
<b>Conductor Insulation Material</b>	PVC/Nylon
<b>Conductor Insulation Color</b>	Black with white numbers and green/yellow ground

<b>Shielding</b>	Unshielded
<b>Jacket Material</b>	TPE
<b>Jacket Color</b>	Black
<b>Nominal Overall Cable Diameter</b>	0.48in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	1 to 50ft = Coil, 51 to 170ft = 14 x 7in Reel, 171 to 240ft = 14 x 10in Reel, 241 to 370ft = 16 x 10in Reel, 371 to 520ft = 18 x 10in Reel, 521 to 680ft = 18 x 13in Reel, 681 to 1470ft = 24 x 17in Wooden Reel, 1471 to 2430ft = 30 x 17in Wooden Reel, 2431 to MAX = Large Wooden Reel

## Agency Approvals

<b>UL Listed File #</b>	E75755
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	90458
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>