

PMTC-18U-9BK-1 Cut Sheet



Southwire flexible power/control cable, unshielded, 9 conductors (includes ground), 18 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PMTC-18U-9BK-1>

Technical Specifications

| | |
|--------------------------------------|--|
| Brand | Southwire |
| Item | Cable |
| Wire/Cable Type | Power/control |
| UL Wire/Cable Type | TC, TC-ER, WTTC and MTW |
| Applicable Standards | ECOLAB |
| Application | General purpose |
| Flexibility | Flexible |
| Voltage Rating | 600V (Types TC, TC-ER, MTW), 1000V (Type WTTC) |
| Conductors | 9 conductors (includes ground) |
| Conductor Size | 18 AWG |
| Conductor Stranding | 16-stranded |
| Conductor Material | Bare copper |
| Conductor Insulation Material | PVC/Nylon |
| Conductor Insulation Color | Black with white numbers and green/yellow ground |

| | |
|---------------------------------------|---|
| Shielding | Unshielded |
| Jacket Material | TPE |
| Jacket Color | Black |
| Nominal Overall Cable Diameter | 0.39in |
| Bulk Length | Cut to length |
| Package Type | <ul style="list-style-type: none">• 20 to 50ft = Coil• 51 to 255ft = 14 x 7in Reel• 256 to 365ft = 14 x 10in Reel• 366 to 560ft = 16 x 10in Reel• 561 to 785ft = 18 x 10in Reel• 786 to 1020ft = 18 x 13in Reel• 1021 to 2285ft = 24 x 17in Wooden Reel• 2286 to 3655ft = 30 x 17in Wooden Reel• 3656 to 5000ft = Large Wooden Reel |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E75755 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | 90458 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |