

# PMU14A Cut Sheet



NITRA pneumatic push-to-connect fitting, inline pressure indicator, technopolymer body, 1/4in tube inlet(s), 1/4in tube outlet(s), 29-145 psi range, orange indication.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PMU14A>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Fitting
<b>Working Fluid</b>	Pneumatic
<b>Fitting Connection Type</b>	Push-to-connect
<b>Fitting Function</b>	Inline pressure indicator
<b>Body Material</b>	Technopolymer
<b>Inlet Port</b>	1/4in tube
<b>Outlet Port</b>	1/4in tube
<b>Pressure Range</b>	29-145 psi
<b>Indicating Type</b>	Orange indication

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>